

HURRICANE



1662201 • Black Frame / Clear Lens



1662202 • Black Frame / Smoke Lens



1662203 • Black Frame / Silver Flash Lens



1662204 • Black Frame / Blue Flash Lens



1662207 • Blue Frame / Blue Flash Lens



1662214 • Black Frame / Light Smoke Silver Flash Lens



1662215 • Black Frame / Polarised Lens



1662209 • Bronze Frame / Silver Flash Lens











26 g

- + LIGHTWEIGHT, CONTOURED FRAME**
- + VELVET FINISH OVER HYDRATED NYLON FRAME**
- + POLARISED LENS TO ELIMINATE GLARE AND REDUCE EYE FATIGUE**
- + ASL ANTI-FOG / ANTI-SCRATCH COATING**

bolle
SAFETY

HURRICANE

MODEL	VERSIONS	REFERENCES	LENS MARKING	FRAME MARKING	COATINGS
HURRICANE	 Clear	1662201	I0	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog
	 Smoke	1662202	I3	AS/NZS 1337.1.2010	Anti-scratch/Anti-fog
	 Silver Flash Lens / Black Frame	1662203	I2	AS/NZS 1337.1.2010	Hard coat
	 Silver Flash Lens / Bronze Frame	1662209	I2	AS/NZS 1337.1.2010	Hard coat
	 Blue Flash Lens / Black Frame	1662204	I2	AS/NZS 1337.1.2010	Hard coat
	 Blue Flash Lens / Blue Frame	1662207	I2	AS/NZS 1337.1.2010	Hard coat
	 Light Smoke Silver Flash Lens	1662214	I2	AS/NZS 1337.1.2010	Hard coat
	 Green Polarised	1662215	I3	AS/NZS 1337.1.2010	Hard coat

LENS MARKING

- I. The letter 'I' signifies 'Medium Impact' approval.
- O. The letter 'O' marking signifies that the product has been approved for the use both outdoors and indoors and the terminology used by Australian standards is 'outdoor un-tinted'. This marking appears on all clear, amber and contrast lenses

OCULAR LENS CATEGORY:

- O. Range of luminous transmittance 80-100% (clear).
2. Range of luminous transmittance 18-43% (flash).
3. Range of luminous transmittance 8-18% (smoke & polarised).

APPLICATIONS

- Assembly and production work
- Process work
- Emergency response
- Driving
- Solar UV exposure
- Laboratory

MAIN MARKETS

- Manufacturing
- Petrochemical
- Construction
- Government
- Mining
- Medical and dental
- Food industry

LENSES

- 2mm polycarbonate
- 8 base curve
- 'ALS' anti-fog/anti-scratch coating on both sides of lens: Clear and Smoke
- Hard coating on Silver and Blue Flash & Polarised lenses
- 100% UV 385 – Clear
- 100% UV 400 – Smoke, Silver Flash, Blue Flash and Polarised

CLEANING AND STORAGE

CLEANING : Bollé Safety recommends only using our **CLEAN** Lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: Store between 5 and 40 °, humidity <90%.

CHARACTERISTICS

LENSES	PC - 2,2 mm - Curve 8
FRAME	Hydrated Nylon
TEMPLES	Hydrated Nylon
STRAP	Non Applicable
FOAM	Non Applicable
SPARE LENSES	No

FRAME MARKING

AS/NZS 1337.1.2010 : Tested and approved to AS/NZS 1337.1.2010 for medium impact protection. Resists a 6mm at 45 m/s.

ASIA/PACIFIC HEADQUARTERS :

Bollé Australia Pty Ltd
32-40 Fairchild Street
Heatherton VIC 3202
T: 1300 138 098
E: safety@bolle.com.au

NEW ZEALAND:

Bollé New Zealand Limited
Unit 5, 114 Sawyers Arms Road
Papanui, Christchurch 8052
T: 03 3751400
E: bolle@bolle.co.nz